

TREMCO-illbruck Foam Gun Spray Cleaner

08/09 2 Pages

PRODUCT

KEY BENEFITS SUMMARY

SPECIAL CLEANER BASED ON ACETONE

- Cleans guns as well as their adaptor
- ☐ Suitable for removing PU-foam that has not cured
- ☐ Removes paint marks, wax, grease, oil and adhesives

PRODUCT INFORMATION

It is possible to clean guns as well as their adaptor with the Gun-/Spray cleaner, screw top and affixed spray Valve top. This cleaner is particularly suitable for removing PU-foam that has not cured. Furthermore, it can be used to remove paint marks, wax, grease, oil and adhesive

PACK SIZE 500ml aerosol PRODUCT CODE 275045

(recyclable with 12 cans/carton)

METHOD OF APPLICATION

As a Spray cleaner

- Put the supplied spray valve onto the valve of the can (hold the valve opening away from the body).
- 2. Point the valve towards the surface to be cleaned and then spray. Allow the cleaner to work for a short time and then clean with a cloth.

As a Gun cleaner

- Unscrew the polyurethane foam (PU-foam) can 1. from the gun (hold the valve opening away from the body)
- 2. Screw the cleaner can onto the gun
- Pull the trigger several times until no polyurethane foam (PU-foam) is dispensed from the gun anymore
- 4. Leave the gun for approx 15 mins to allow the cleaner to work
- 5. Pull the trigger once more to remove any residue polyurethane
- 6. Unscrew the cleaner from the gun
- 7. If gun is to be stored, close valve adjustment screw at back of gun to prevent solvent loss
- 8. When connecting a new can of polyurethane foam pull release adjustment screw or pull trigger several times to remove remain of cleaner

STORAGE

Store in dry conditions below 25°C

Company

SHELF LIFE

12 months when stored as recommended in original ened containers

HEALTH & SAFETY PRECAUTIONS

Material Safety Data Sheet (MSDS) must be read and understood prior to use.

STORAGE

Store in dry conditions below 25°C

SHELF LIFE

12 months when stored as recommended in original unopened containers

HEALTH & SAFETY PRECAUTIONS

Material Safety Data Sheet (MSDS) must be read and understood prior to use.

TECHNICAL SERVICE

TREMCO has a team of qualified Technical Sales Representatives who provide assistance in the selection and specification of products. For more detailed information or service and advice, call Customer Service on (02) 9638 2755 or fax on (02) 9638 2955

GUARENTEE/WARRANTY

TREMCO products are manufactured to rigid standards of quality. Any product which has been applied (a) in accordance with TREMCO written instructions and (b) in any application recommended by TREMCO, but which is proved to be defective, will be replaced free of charge.

Any information provided by TREMCO in this document in relation to TREMCO's goods or their use is given in good faith and is believed by TREMCO to be appropriate and reliable. However, the information is provided as a guide only, as the actual size and application will vary with application conditions which are beyond our control. TREMCO makes no representation, guarantee or warranty relating to the accuracy or reliability of the information and assumes no obligation or liability in connection with the information. To the extent permitted by law, all warranties, expressed or implied are excluded.

TREMCO PTY LTD ABN 25 000 024 064 Unit 1, 2 Park Rd, RYDALMERE NSW 2116 Australia Tel (02) 9638 2755 Fax (02) 9638 2955 Tremco@Tremco.com.au